

OVERVIEW

The Vertiv Geist FSC, Facility Side Cable, features a universal connector designed to mate with the Universal Input on the Vertiv Geist UPDU, Universal Power Distribution Unit. The FSC is available in common worldwide AC power specs ranging from 16A to 60A, 120V to 415V with single and three phase power configurations. Select the detachable Vertiv Geist FSC specific to the local power configuration to power the UPDU. (UPDU sold separately)

Benefits

- The flexibility offered by the UPDU and FSC enable any rack architecture to be installed in any data center around the world, regardless of the power infrastructure already in place.
- The FSC enables users to utilize a single UPDU model with various input power configurations to simplify global IT infrastructure deployments, inventory management and enable rapid deployments worldwide.
- Increase or decrease UPDU power capacity by changing the FSC to adapt to fluctuating equipment power needs.
- Every unit is 100% tested for reliability and functionality to ensure units function as designed.



Part #: FSC3U002

Model Number: CSU-S02A3-43000-3PS56B-S

Category: Facility Side Cable

Sub Category: Standard

Power Configuration: 30 OR 32A, 230/400V WYE, 22.0kW

Physical Configuration: 10ft / 3m Facility Side Cable

Product Summary:

FSC3U002 - Facility Side Cable, 30/32A, 230/400V WYE, 22.0kW, 10ft / 3m with IEC 3P+N+E (IP44) and Universal Connector.

Plug Form:



3P+N+E (IP44)

Receptacle:



Universal Connector
(Quantity: 1)

Chassis Color Options:



To discuss color options, contact your local sales representative.

Product Specification and Options

System Features

| | |
|------------------------------------|---|
| Compatibility | For use with Vertiv Geist Universal Rack PDU (UPDU) |
| Voltage | 208-240/360-415V WYE |
| Current | 30/32A x 3 Phase WYE |
| Frequency | 50/60Hz |
| Power Cable Wire Gauge | 9/5 (6mm ²) |
| Power Cable Length | 10ft / 3m |
| Plug Type | IEC60309 3P + N + E, 30/32A, 230/400V, Splashproof IP44 |
| Max Plug kW | 22.0kW (230V) |
| Output Connector | Universal Connector |
| UPDU Voltage per Receptacle/Socket | 208-240V |
| Product Warranty | 5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years |
| Certification/Agency Approvals | CE Marked |
| Certification/Agency Approvals | Complies with EN 55032 and EN 55024 |
| Certification/Agency Approvals | Complies with IEC 60950-1 (CB Certificate Available) |
| Certification/Agency Approvals | RoHS Compliant |
| Certification/Agency Approvals | UL & c-UL Listed 60950 |
| Shipped Weight | 6lbs (2.72kg) |