

CYBEX™ SC800 SECURE DESKTOP KVM SWITCHES

Outstanding security and control at the desktop



BENEFITS

- Outstanding Security:**
 - Certified to NIAP Protection Profile for Peripheral Switching Switches, version 3.0
 - Unidirectional Optical Data Diodes assure USB peripheral isolation enabling data flow from devices to host only
 - Hardware-based peripheral isolation loads all firmware on ROM with no keyboard buffering or memory
 - Full USB device filtering to assure support for keyboard and mouse only
 - Dedicated Peripheral Port permits a secure connection to external USB devices, including CAC smart card readers, fingerprint readers and face recognition devices
 - Always-on active anti-tampering system
- Access:** Access multiple computers or networks using a single keyboard, monitor and mouse
- Advanced Video Support:** Support for DVI-I, HDMI 1.4 and DP1.2 in single and dual head models supporting high resolutions up to UHD 4K
- Zero Delay Switching:** Mouse and keyboard switching via emulation assures zero delay in switching time between connected sources



Specifications

PART NUMBER	SC840 SC845	SC840D SC845D	SC840H SC845H
System Connections	4	4	4
System Support	DVI-I, single-link/dual-link	DisplayPort 1.2	HDMI 1.4
Display Connections	1	1	1
Display Support	DVI-I, single-link, dual-link	HDMI 1.4	HDMI 1.4
Max Resolution	DVI dual-link - 2560X1600 @ 60 Hz	UHD 4K - 3840x2160 @30 Hz	UHD 4K - 3840x2160 @30 Hz

SECURITY FEATURES	
Console Peripherals	USB Type-A
Computer Peripherals	USB Type-B
Audio Input/Output	2 x 3.5mm stereo female
MECHANICAL	
Enclosure	Steel with Plastic Front Panel
Dimensions WxDxH	342 x 125 x 42 mm 13.7 x 5 x 1.7 inches
Weight	1.6 kg (3.2 lbs)
POWER	
Power Requirements	35W Max Internal
AC Input Voltage	100 to 240V AC
ENVIRONMENTAL	
Operating Temperature	32° to 104° F; 0° to 40° C
Storage Temperature	-4° to 140° F; -20° to 60° C
Humidity	0-80% RH, non-condensing
Certifications	CE, RCM, FCC class B, VCCI, TUV US, TUV Canada
Warranty	3 years



SC845D

Ordering Details

Cybex™ Desktop KVM Cables		
PART NUMBER	MODEL	DETAILS
CBLO094	SC840	USB keyboard, mouse & DVI-I video cable with speakers - 6 ft.
CBLO095	SC840	USB keyboard, mouse & DVI-I video cable with speakers - 10 ft.
CBLO096	SC845	USB keyboard, mouse & DVI-I video cable with speakers & CAC - 6 ft.
CBLO097	SC845	USB keyboard, mouse & DVI-I video cable with speakers & CAC - 10 ft.
CBLO102	SC840D	USB keyboard, mouse & DisplayPort video cable with speakers - 6 ft.
CBLO104	SC845D	USB keyboard, mouse & DisplayPort video cable with speakers & CAC - 6 ft.
CBLO110	SC840H	USB keyboard, mouse & HDMI video cable with speakers - 6 ft.
CBLO111	SC840H	USB keyboard, mouse & HDMI video cable with speakers - 10 ft.
CBLO112	SC845H	USB keyboard, mouse & HDMI video cable with speakers & CAC - 6 ft.
CBLO113	SC845H	USB keyboard, mouse & HDMI video cable with speakers & CAC - 10 ft.

VertivCo.com | Vertiv Headquarters, 1050 Dearborn Drive, Columbus, OH, 43085, USA

© 2016 Vertiv Co. All rights reserved. Vertiv and the Vertiv logo are trademarks or registered trademarks of Vertiv Co. All other names and logos referred to are trade names, trademarks or registered trademarks of their respective owners. While every precaution has been taken to ensure accuracy and completeness herein, Vertiv Co. assumes no responsibility, and disclaims all liability, for damages resulting from use of this information or for any errors or omissions. Specifications are subject to change without notice.

CYBEX™ SC900 SECURE DESKTOP KVM SWITCHES

Outstanding security and control at the desktop



BENEFITS

- Outstanding Security:**
 - Certified to NIAP Protection Profile for Peripheral Switching Devices, version 3.0
 - Unidirectional Optical Data Diodes assure USB peripheral isolation enabling data flow from devices to host only
 - Hardware-based peripheral isolation loads all firmware on ROM with no keyboard buffering or memory
 - Full USB device filtering to assure support for keyboard and mouse only
 - Dedicated Peripheral Port permits a secure connection to external USB devices, including CAC smart card readers, fingerprint readers and face recognition devices
 - Always-on active anti-tampering system
- Access:** Access multiple computers or networks using a single keyboard, monitor and mouse
- Advanced Video Support:** Support for DVI-I, HDMI 1.4 and DP1.2 in single and dual head models supporting high resolutions up to UHD 4K
- Zero Delay Switching:** Mouse and keyboard switching via emulation assures zero delay in switching time between connected sources



Specifications

PART NUMBER	SC940 SC945	SC940D SC945D	SC940H SC945H
System Connections	4	4	4
System Support	DVI-I, single-link/dual-link	DisplayPort 1.2	HDMI 1.4
Display Connections	2	2	2
Display Support	DVI-I, single-link/dual-link	HDMI 1.4	HDMI 1.4
Max Resolution	DVI dual-link - 2560X1600 @ 60 Hz	UHD 4K - 3840X2160 @ 30 Hz	UHD 4K - 3840X2160 @ 30 Hz

SECURITY FEATURES

Console Peripherals	USB Type-A
Computer Peripherals	USB Type-B
Audio Input/Output	2 x 3.5mm stereo female

MECHANICAL

Enclosure	Steel with Plastic Front Panel
Dimensions WxDxH	342 x 125 x 56 mm 13.7 x 5 x 2.2 inches
Weight	1.85 kg /(3.7 lbs)

POWER

Power Requirements	35W Max Internal
AC Input Voltage	100 to 240V AC

ENVIRONMENTAL

Operating Temperature	32° to 104° F; 0° to 40° C
Storage Temperature	-4° to 140° F; -20° to 60° C
Humidity	0-80% RH, non-condensing

Certifications CE, RCM, FCC class B, VCCI, TUV US, TUV Canada

Warranty 3 years



SC940D

Ordering Details

Cybox™ Desktop KVM Cables

PART NUMBER	MODEL	DETAILS
CBL0098	SC940	USB keyboard, mouse & dual head DVI-I video cable with speakers - 6 ft.
CBL0099	SC940	USB keyboard, mouse & dual head DVI-I video cable with speakers - 10 ft.
CBL0100	SC945	USB keyboard, mouse & dual head DVI-I video cable with speakers & CAC - 6 ft.
CBL0101	SC945	USB keyboard, mouse & dual head DVI-I video cable with speakers & CAC - 10 ft.
CBL0106	SC940D	USB keyboard, mouse & dual head DisplayPort video cable with speakers - 6 ft.
CBL0108	SC945D	USB keyboard, mouse & dual head DisplayPort video cable with speakers & CAC - 6 ft.
CBL0114	SC940H	USB keyboard, mouse & dual head HDMI video cable with speakers - 6 ft.
CBL0115	SC940H	USB keyboard, mouse & dual head HDMI video cable with speakers - 10 ft.
CBL0116	SC945H	USB keyboard, mouse & dual head HDMI video cable with speakers & CAC - 6 ft.
CBL0117	SC945H	USB keyboard, mouse & dual head HDMI video cable with speakers & CAC - 10 ft.

VertivCo.com | Vertiv Headquarters, 1050 Dearborn Drive, Columbus, OH, 43085, USA

© 2016 Vertiv Co. All rights reserved. Vertiv and the Vertiv logo are trademarks or registered trademarks of Vertiv Co. All other names and logos referred to are trade names, trademarks or registered trademarks of their respective owners. While every precaution has been taken to ensure accuracy and completeness herein, Vertiv Co. assumes no responsibility, and disclaims all liability, for damages resulting from use of this information or for any errors or omissions. Specifications are subject to change without notice.