


## OVERVIEW

Upgradeable Switched Unit Level Monitored EC rPDUs provide reliable power distribution to critical IT equipment while delivering individual outlet level control and a comprehensive view of input power usage via remote network access. Includes environmental monitoring capabilities to obtain real-time environmental metrics. Upgrade the hot-swappable monitoring device on select units to leverage new technologies and accommodate changing business needs.

### Benefits

- Remotely reboot outlets to power cycle unresponsive IT equipment or increase runtime of critical equipment upon power failure with outlet-level control.
- Reliable power distribution with local and remote power monitoring options offer quick access to critical power usage information to evaluate energy usage trends and maximize uptime.
- Environmental monitoring capabilities with the addition of optional environmental sensors ensure users have critical infrastructure data at their fingertips to prevent climate-related equipment failure and system downtime.
- Fault-Tolerant Daisy Chaining with RSTP simplifies intelligent rPDU connectivity and ensures data is reported even when a break in the network chain occurs. Supports up to 40 rPDUs.



## Part #: VP51100

**Model Number:** MNS3E1R5-06S153-1ST5A0H10-S

**Category:** Switched

**Sub Category:** Unit Level Monitoring EC

**Power Configuration:** 15A, 120V, 1.4kW

**Physical Configuration:** 19in / 483mm, Horizontal

### Product Summary:

rPDU, Switched Unit Level Monitoring EC, 15A, 120V, 1.4kW, Horizontal, (6) NEMA 5-15R, 10ft / 3m power cord with 5-15P, Black Powder Coat.

### Monitoring:

Input power monitoring with Outlet switching. Environmental monitoring via optional remote sensors. Daisy chain Ethernet connectivity. Local high visibility LED display.

### Plug Form:



5-15P

### Receptacle:



NEMA 5-15R  
(Quantity: 6)

### Chassis Color Options:



To discuss color options, contact your local sales representative.

## Product Specification and Options

### System Features

<b>Monitoring</b>	Input power monitoring with Outlet switching. Environmental monitoring via optional remote sensors. Daisy chain Ethernet connectivity. Local high visibility LED display.
<b>Input Monitoring</b>	Phase (A) Monitoring (kWh, W, VA, PF, V, A)  Power Measurements Compliant with ANSI C12.1 and IEC 62053-21 at 1% Accuracy Class Requirements
<b>Remote Power Management</b>	Individual Outlet Switching with Optional User Defined Time Delays and Sequential Power-up
<b>Quantity Of Inputs</b>	1
<b>Voltage</b>	100-120V
<b>Current</b>	15A
<b>VA per Input (Load Capacity)</b>	1.4kW (120V)
<b>Frequency</b>	50/60Hz
<b>Over Current Protection</b>	None
<b>Switch</b>	No
<b>Scrolling / Rotatable Digital Display</b>	Yes
<b>Indicators - LED(s)</b>	6
<b>Power Cable Wire Gauge</b>	14/3
<b>Power Cable Length</b>	10ft / 3m
<b>Power Entry Location</b>	Left Rear
<b>Plug Type</b>	NEMA 5-15P
<b>Receptacle/Socket Type #1</b>	NEMA 5-15R
<b>- Quantity on Rear</b>	6
<b>- Style</b>	Individual
<b>- Voltage per Receptacle/Socket</b>	120V
<b>Network Connection</b>	Dual 10/100/1000Mbps Ethernet
<b>Protocols Supported</b>	DHCP, HTTP, HTTPS, IPv4, IPv6, LDAP, NTP, RADIUS, RSTP, SSH, SMTP, SNMP (v1/v2c/v3), Syslog, TACACS+
<b>Data Access Formats</b>	CSV datalog, JSON API, JSON datalog
<b>USB Support</b>	Yes
<b>IP Reset Button</b>	Yes
<b>Hard Reboot Button</b>	Yes
<b>Serial Connection</b>	RS232 via RJ45
<b>Remote Sensor RJ Connection Jacks</b>	1 (Supports up to 16 Sensors)
<b>Maximum Operating Temperature</b>	60C / 140F
<b>Heavy Steel - Powder Coat Finish</b>	Black
<b>Configuration</b>	19in / 483mm Horizontal Rackmount
<b>Adjustable Mount Brackets</b>	Yes
<b>Country of Origin</b>	USA, TAA Compliant and Buy American Act COTS Compliant
<b>Product Warranty</b>	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
<b>Certification/Agency Approvals</b>	FCC Part 15 Class A Conformance
<b>Certification/Agency Approvals</b>	RoHS Compliant

<b>Certification/Agency Approvals</b>	UL & c-UL Listed 62368-1
<b>Chassis Dimensions (HxWxD)</b>	1.72in x 17in x 12in / 44mm x 432mm x 305mm
<b>Shipped Weight</b>	10lbs (4.54kg)